FABORY

Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M10X50

Article number	24540.100.050
Brand	-
UBB	950353140201
UNSPSC	31161504
EAN	8715492634085
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
BS	≈4183
NF	≈E25-123
ASME	≈B18.6.7M
NEN	≈2370
DIN	963

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if L ≤	50
k (max.)	5
L (mm)	50
n	2.5
P	1.5
t (min.)	2

Technical Drawing