

## Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M10X50



Article number 24540.100.050

Brand -

UBB 950353140201

UNSPSC 31161504

EAN 8715492634085

PKG. of 100 Full Box Only

### Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	50
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

NF	≈E25-123
ASME	≈B18.6.7M
DIN	963
ISO	≈2009
BS	≈4183

### Technical Specification

Thread length (min.)	40
$d_k$ (max.)	18
Full thread if $L \leq$	50
$k$ (max.)	5
$n$	2.5
$P$	1.50
$t$ (min.)	2

### Technical Drawing

