



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M12X50

Article number	24540.120.050
Brand	-
UBB	950353141290
UNSPSC	31161504
EAN	8715492634214
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
ASME	≈B18.6.7M
NF	≈E25-123
NEN	≈2370
DIN	963
BS	≈4183

Technical Specification

d-D	M12
Thread length (min.)	46
dk (max.)	22
Full thread if $L \leq$	60
k (max.)	6
L (mm)	50
n	3
P	1.75
t (min.)	2.4

Technical Drawing

