

Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M20X60



Article number	24540.200.060
Brand	-
UBB	950353142934
UNSPSC	31161504
EAN	8715492634429
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M20
Length (L) (mm)	60
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	963
BS	≈4183
NF	≈E25-123
ISO	≈2009

Technical Specification

Thread length (min.)	70
d_k (max.)	36
Full thread if $L \leq$	80
k (max.)	10
n	5
P	2.50
t (min.)	4

Technical Drawing

