



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M4X20

Article number	24560.040.020
Brand	-
UBB	950353144757
UNSPSC	31161504
EAN	8715492634818
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
NEN	≈2370
DIN	963
ISO	≈2009
ASME	≈B18.6.7M

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	20
n	1
P	0.7
t (min.)	0.8

Technical Drawing

