



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M5X10

Article number	24560.050.010
Brand	-
UBB	950353145176
UNSPSC	31161504
EAN	8715492634894
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NF	≈E25-123
ISO	≈2009
BS	≈4183
NEN	≈2370
DIN	963

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	10
n	1.2
P	0.8
t (min.)	1

Technical Drawing

