



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M5X12

Article number	24560.050.012
Brand	-
UBB	950353145259
UNSPSC	31161504
EAN	8715492634900
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

BS	≈4183
ISO	≈2009
NEN	≈2370
DIN	963
NF	≈E25-123
ASME	≈B18.6.7M

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	12
n	1.2
P	0.8
t (min.)	1

Technical Drawing

