

Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M5X30



Article number 24560.050.030

Brand -

UBB 950353145663

UNSPSC 31161504

EAN 8715492634948

PKG. of 500 Full Box Only

Technical Parameters

| | |
|-------------------|-------------------------------|
| Diameter (d-D) | M5 |
| Length (L) (mm) | 30 |
| Class | 4.8 |
| Driving features | Slotted |
| Head shape | Countersunk head |
| Material | Steel |
| Surface treatment | Zinc plated yellow passivated |
| Thread | Metric thread |

Standards

| | |
|------|-----------|
| DIN | 963 |
| NF | ≈E25-123 |
| ASME | ≈B18.6.7M |
| ISO | ≈2009 |
| BS | ≈4183 |

Technical Specification

| | |
|-------------------------|------|
| Thread length (min.) | 25 |
| d_k (max.) | 9.2 |
| Full thread if $L \leq$ | 30 |
| k (max.) | 2.5 |
| n | 1.2 |
| P | 0.80 |
| t (min.) | 1 |

Technical Drawing

