



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M4X8

Article number	24565.040.008
Brand	-
UBB	950353912591
UNSPSC	31161504
EAN	8715492635327
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

DIN	963
NF	≈E25-123
ISO	≈2009
BS	≈4183
NEN	≈2370
ASME	≈B18.6.7M

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	8
n	1
P	0.7
t (min.)	0.8

Technical Drawing

