



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M5X35

Article number	24565.050.035
Brand	-
UBB	950353913748
UNSPSC	31161504
EAN	8715492635471
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

NF	≈E25-123
DIN	963
ISO	≈2009
NEN	≈2370
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	35
n	1.2
P	0.8
t (min.)	1

Technical Drawing

