



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M8X16

Article number	24565.080.016
Brand	-
UBB	950353914241
UNSPSC	31161504
EAN	8715492635631
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

BS	≈4183
ISO	≈2009
ASME	≈B18.6.7M
NEN	≈2370
NF	≈E25-123
DIN	963

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	16
n	2
P	1.25
t (min.)	1.6

Technical Drawing

