



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M3X12

Article number	24570.030.012
Brand	-
UBB	950353147644
UNSPSC	31161504
EAN	8715492635884
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NEN	≈2371
DIN	964
NF	≈E25-124
ISO	≈2010
ASME	≈B18.6.7M

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	12
n	0.8
P	0.5
t (min.)	1.2

Technical Drawing

