



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M5X60

Article number	24570.050.060
Brand	-
UBB	950353150432
UNSPSC	31161504
EAN	8715492636232
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NEN	≈2371
NF	≈E25-124
ASME	≈B18.6.7M
ISO	≈2010
DIN	964

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	60
n	1.2
P	0.8
t (min.)	2

Technical Drawing

