



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M6X12

Article number	24570.060.012
Brand	-
UBB	950353150689
UNSPSC	31161504
EAN	8715492636263
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2371
ASME	≈B18.6.7M
NF	≈E25-124
ISO	≈2010
DIN	964
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	12
n	1.6
P	1
t (min.)	2.4

Technical Drawing

