



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M6X30

Article number	24570.060.030
Brand	-
UBB	950353151000
UNSPSC	31161504
EAN	8715492636300
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
ISO	≈2010
DIN	964
NF	≈E25-124
NEN	≈2371

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	30
n	1.6
P	1
t (min.)	2.4

Technical Drawing

