



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M6X40

Article number	24570.060.040
Brand	-
UBB	950353151265
UNSPSC	31161504
EAN	8715492636324
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	964
NEN	≈2371
ASME	≈B18.6.7M
ISO	≈2010
NF	≈E25-124
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	40
n	1.6
P	1
t (min.)	2.4

Technical Drawing

