



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M8X30

Article number	24570.080.030
Brand	-
UBB	950353151836
UNSPSC	31161504
EAN	8715492636393
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	964
NF	≈E25-124
BS	≈4183
ASME	≈B18.6.7M
NEN	≈2371
ISO	≈2010

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
f ≈	2
Full thread if L ≤	40
k (max.)	4
L (mm)	30
n	2
P	1.25
t (min.)	3.2

Technical Drawing

