



Slotted pan head screw DIN 85 Steel Plain 4.8 M6X16

Article number	24635.060.016
Brand	-
UBB	500649350476
UNSPSC	31161504
EAN	8717077266025
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M6
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	≈1603
NF	≈E25-128
DIN	85
BS	≈4183
ASME	≈B18.6.7M
ISO	≈1580

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	12
Full thread if $L \leq$	40
k (max.)	3.6
L (mm)	16
n	1.6
P	1
t (min.)	1.4

Technical Drawing

