



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M3X30

Article number	24640.030.030
Brand	-
UBB	950353153162
UNSPSC	31161504
EAN	8715492637062
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

BS	≈4183
NF	≈E25-128
ISO	≈1580
NEN	≈1603
ASME	≈B18.6.7M
DIN	85

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if $L \leq$	30
k (max.)	1.8
L (mm)	30
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

