



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M4X6

Article number	24640.040.006
Brand	-
UBB	950353153329
UNSPSC	31161504
EAN	8715492637260
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	6 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

ASME	≈B18.6.7M
DIN	85
ISO	≈1580
NF	≈E25-128
BS	≈4183
NEN	≈1603

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	8
Full thread if $L \leq$	40
k (max.)	2.4
L (mm)	6
n	1.2
P	0.7
t (min.)	1

Technical Drawing

