



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M4X20

Article number	24640.040.020
Brand	-
UBB	950353153816
UNSPSC	31161504
EAN	8715492637338
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

NEN	≈1603
NF	≈E25-128
ISO	≈1580
DIN	85
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	8
Full thread if $L \leq$	40
k (max.)	2.4
L (mm)	20
n	1.2
P	0.7
t (min.)	1

Technical Drawing

