



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M5X30

Article number	24640.050.030
Brand	-
UBB	950353154806
UNSPSC	31161504
EAN	8715492637550
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

BS	≈4183
ISO	≈1580
DIN	85
NF	≈E25-128
NEN	≈1603
ASME	≈B18.6.7M

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	10
Full thread if $L \leq$	40
k (max.)	3
L (mm)	30
n	1.2
P	0.8
t (min.)	1.2

Technical Drawing

