



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M5X60

Article number	24640.050.060
Brand	-
UBB	950353630847
UNSPSC	31161504
EAN	8715492637611
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

ISO	≈1580
NEN	≈1603
ASME	≈B18.6.7M
DIN	85
BS	≈4183
NF	≈E25-128

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	10
Full thread if $L \leq$	40
k (max.)	3
L (mm)	60
n	1.2
P	0.8
t (min.)	1.2

Technical Drawing

