



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M6X12

Article number	24640.060.012
Brand	-
UBB	950353155308
UNSPSC	31161504
EAN	8715492637659
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

BS	≈4183
NEN	≈1603
NF	≈E25-128
ASME	≈B18.6.7M
DIN	85
ISO	≈1580

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	12
Full thread if $L \leq$	40
k (max.)	3.6
L (mm)	12
n	1.6
P	1
t (min.)	1.4

Technical Drawing

