



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M6X16

Article number	24640.060.016
Brand	-
UBB	950353155480
UNSPSC	31161504
EAN	8715492637666
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

BS	≈4183
NEN	≈1603
DIN	85
ISO	≈1580
ASME	≈B18.6.7M
NF	≈E25-128

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	12
Full thread if $L \leq$	40
k (max.)	3.6
L (mm)	16
n	1.6
P	1
t (min.)	1.4

Technical Drawing

