



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M6X20

Article number	24640.060.020
Brand	-
UBB	950353155555
UNSPSC	31161504
EAN	8715492637680
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

ISO	≈1580
NF	≈E25-128
ASME	≈B18.6.7M
BS	≈4183
DIN	85
NEN	≈1603

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	12
Full thread if $L \leq$	40
k (max.)	3.6
L (mm)	20
n	1.6
P	1
t (min.)	1.4

Technical Drawing

