



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M8X25

Article number	24640.080.025
Brand	-
UBB	950353629385
UNSPSC	31161504
EAN	8715492637840
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

NEN	≈1603
BS	≈4183
ISO	≈1580
DIN	85
ASME	≈B18.6.7M
NF	≈E25-128

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	4.8
L (mm)	25
n	2
P	1.25
t (min.)	1.9

Technical Drawing

