



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M6X80

Article number	24671.060.080
Brand	-
UBB	500621769743
UNSPSC	31161504
EAN	8715494509305
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	80 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

Standards

DIN	965
NF	≈E25-119-1
ISO	≈7046-1

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if L ≤	35
k (max.)	3

Technical Drawing

L (mm) 80

No. cross recess 3

P 1

