



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated black passivated 4.8 M3X6

Article number	24840.030.006
Brand	-
UBB	950353176684
UNSPSC	31161504
EAN	8715492645357
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

ISO	≈7046-1
DIN	965
NF	≈E25-119-1

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	6
No. cross recess	1
P	0.5

Technical Drawing

