



Slotted raised countersunk head tapping screw DIN 7973 C Steel Nickel plated ST2,9X19MM

Article number	26040.029.019
Brand	-
UBB	950352051607
UNSPSC	31161507
EAN	8715492651341
PKG. of 200	Full Box Only

Technical Parameters

Diameter	2.9 mm
Length	19 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

BS	4174
NF	E25-661 C
ISO	1483 C
DIN	7973 C

Technical Specification

D (mm)	2.9
dk	5.5
f ≈	0.9
k ≈	1.7
L (mm)	19
n	0.8
P	1.5

Technical Drawing

