



Slotted raised countersunk head tapping screw DIN 7973 C Steel Nickel plated ST3,5X19MM

Article number	26040.035.019
Brand	-
UBB	950352052100
UNSPSC	31161507
EAN	8715492651396
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	19 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-661 C
ISO	1483 C
BS	4174
DIN	7973 C

Technical Specification

D (mm)	3.5
dk	6.8
f ≈	1.2
k ≈	2.1
L (mm)	19
n	1
P	1.3

Technical Drawing

