



Slotted raised countersunk head tapping screw DIN 7973 C Steel Nickel plated ST5,5X50MM

Article number	26040.055.050
Brand	-
UBB	950352055418
UNSPSC	31161507
EAN	8715492651761
PKG. of 100	Full Box Only

Technical Parameters

Diameter	5.5 mm
Length	50 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ISO	1483 C
BS	4174
NF	E25-661 C
DIN	7973 C

Technical Specification

D (mm)	5.5
dk	10.8
f ≈	1.7
k ≈	3.4
L (mm)	50
n	1.6
P	1.8

Technical Drawing

