



Cross recessed pan head tapping screw Phillips DIN 7981 C-H Steel Nickel plated ST2,9X13MM

Article number	26200.029.013
Brand	-
UBB	950352064659
UNSPSC	31161507
EAN	8715492652829
PKG. of 200	Full Box Only

Technical Parameters

Diameter	2.9 mm
Length	13 mm
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ASME	B18.6.4
NF	E25-658
DIN	7981 CH
ISO	7049 CH

Technical Specification

D (mm)	2.9
dk	5.6
k	2.2
L (mm)	13
No. cross recess	1
P	1.1

Technical Drawing

