



Cross recessed pan head tapping screw Phillips DIN 7981 C-H Steel Nickel plated ST3,9X16MM

Article number	26200.039.016
Brand	-
UBB	950352065987
UNSPSC	31161507
EAN	8715492652959
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.9 mm
Length	16 mm
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-658
ASME	B18.6.4
DIN	7981 CH
ISO	7049 CH

Technical Specification

D (mm)	3.9
dk	7.5
k	2.8
L (mm)	16
No. cross recess	2
P	1.4

Technical Drawing

