



## Cross recessed pan head tapping screw Phillips DIN 7981 C-H Steel Nickel plated ST3,9X19MM

|                |               |
|----------------|---------------|
| Article number | 26200.039.019 |
| Brand          | -             |
| UBB            | 950352066068  |
| UNSPSC         | 31161507      |
| EAN            | 8715492652966 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |                     |
|-------------------|---------------------|
| Diameter          | 3.9 mm              |
| Length            | 19 mm               |
| Driving features  | Phillips            |
| Head shape        | Pan head            |
| Material          | Steel               |
| Surface treatment | Nickel plated       |
| Thread            | Self tapping thread |

Info      Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.

### Standards

|      |         |
|------|---------|
| ISO  | 7049 CH |
| DIN  | 7981 CH |
| NF   | E25-658 |
| ASME | B18.6.4 |

### Technical Specification

|                  |     |
|------------------|-----|
| D (mm)           | 3.9 |
| dk               | 7.5 |
| k                | 2.8 |
| L (mm)           | 19  |
| No. cross recess | 2   |
| P                | 1.4 |

### Technical Drawing

