



Hexalobular socket pan head tapping screw ISO 14585 C Steel Zinc plated ST4,8X9,5MM

Article number	26501.048.009
Brand	-
UBB	500645233718
UNSPSC	31161507
EAN	8717077064874
PKG. of 500	Full Box Only

Technical Parameters

Diameter	4.8 mm
Length	9.5 mm
Driving features	Hexalobular
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread

Standards

ISO	14585 C
-----	---------

Technical Specification

D (mm)	4.8
dk (max.)	9.5
k (max.)	3.7
L (mm)	9.5
P	1.6
Socket	25

Technical Drawing

