



Cross recessed countersunk head tapping screw Phillips DIN 7982 C-H Steel Zinc plated ST3,5X6,5MM

Article number	26680.035.006
Brand	-
UBB	500645244038
UNSPSC	31161507
EAN	8717077065901
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	6.5 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	7982 CH
NF	E25-656
ISO	7050 CH

Technical Specification

D (mm)	3.5
dk	6.8
k ≈	2.1
L (mm)	6.5
No. cross recess	2
P	1.3

Technical Drawing

