



Cross recessed countersunk head tapping screw Phillips DIN 7982 C-H Steel Zinc plated ST3,9X38MM

Article number	26680.039.038
Brand	-
UBB	500645244111
UNSPSC	31161507
EAN	8717077065918
PKG. of 500	Full Box Only

Technical Parameters

Diameter	3.9 mm
Length	38 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-656
DIN	7982 CH
ISO	7050 CH

Technical Specification

D (mm)	3.9
dk	7.5
k ≈	2.3
L (mm)	38
No. cross recess	2
P	1.4

Technical Drawing

