



Cross recessed countersunk head screw for chipboard Pozidriv Steel Zinc plated 6X120MM

Article number	29240.060.120
Brand	-
UBB	950350034415
UNSPSC	31161508
EAN	8715492953131
PKG. of 200	Full Box Only

Technical Parameters

Diameter	6 mm
Length	120 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Info	All dimensions are guide values and may deviate dependent on the manufacturer. Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

Technical Specification

D (mm)	6
dk (max.)	11.6
k (max.)	3.6
L (mm)	120
No. cross recess	3

Technical Drawing

