

Dormer Jobber drill A002
DIN 338 HSS Blanc/TiN
8.20mm



Article number	2N012642
Brand	-
UBB	500631114831
UNSPSC	23241639
EAN	7320760351222
PKG. of 10	Full Box Only

Technical Parameters

Total length	117
Diameter drill	8.2
Holding system	Cylindrical plug-in axle
Cutting length	75
Cutting material	HSS
Shank shape	Cylindrical
Spiral drill	Yes

Standards