



MAXXFAST Self-drilling screw hexagon head DIN ≈7504 K Bi-Metal ST6,3X50MM

Article number	30420.063.050
Brand	-
UBB	500618374366
UNSPSC	31162400
EAN	8715494506007
PKG. of 200	Full Box Only

Technical Parameters

Diameter	6.3 mm
Length	50 mm
Driving features	Hexagon
Head shape	Hexagon head
Material	Bi-Metal
Thread	Self tapping thread
Info	Full boxes only.

Standards

ISO	≈15480
DIN	≈7504-K

Technical Specification

dc (max.)	13.5
D (mm)	6.3
k (max.) - 30410	5.9
k (max.) - 30415	5.9
k (max.) - 30420	6.45
L (mm)	50
L1	7.5
s	10

Technical Drawing

