



Self-drilling cross recessed pan head screw Phillips DIN 7504 M-H Steel Zinc plated large pack ST4,8X110MM

Article number	31820.048.110
Brand	-
UBB	500645273151
UNSPSC	31161507
EAN	8717077074088
PKG. of 100	Full Box Only

Technical Parameters

Diameter	4.8 mm
Length	110 mm
Application (metal)	Aluminium
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread
Info	Max. grip length KL = L - L1. Warning: electroplating of these products may cause hydrogen embrittlement. large pack

Standards

ISO	15481 H
DIN	7504-M H

Technical Specification

D (mm)	4.8
dk	9.5
k	3.55
L (mm)	110
L1 ≈	8
No. cross recess	2
P	1.6

Technical Drawing

