



Bearing preload disc spring Spring steel Phosphated 12,8X7,2X0,25MM

| | |
|-------------|---------------|
| Article No. | 36460.135.002 |
| Brand | - |
| UBB | 950357386321 |
| UNSPSC | 31161811 |
| EAN | 8715492762979 |
| PKG. of 100 | Full Box Only |

Technical Parameters

| | |
|-------------------|--|
| De | 12.8 |
| Di | 7.2 |
| Diameter (mm) | 7.2 |
| t | 0.25 |
| Info | F = spring load in Newton at a deflection $s \approx 0,75 h_0$ ($h_0 = l_0 - t$). Extensive technical data available on request. |
| Material | Spring steel |
| Outer diameter | 12.8 |
| Surface treatment | Phosphated |
| Thickness | 0.25 mm |
| Info | Warning: electroplating of these products may cause hydrogen embrittlement. |

Standards

Technical Specification

| | |
|----------------------|-----|
| D _i (H12) | 7.2 |
| F | 29 |
| l ₀ | 0.5 |

Technical Drawing

t

0.25

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS

