



Bearing preload disc spring Spring steel Phosphated 46,5X30,5X0,6MM

| | |
|-------------|---------------|
| Article No. | 36460.495.006 |
| Brand | - |
| UBB | 950357387154 |
| UNSPSC | 31161811 |
| EAN | 8715492763105 |
| PKG. of 25 | Full Box Only |

Technical Parameters

| | |
|-------------------|--|
| De | 46.5 |
| Di | 30.5 |
| Diameter (mm) | 30.5 |
| t | 0.6 |
| Info | F = spring load in Newton at a deflection $s \approx 0,75 h_0$ ($h_0 = l_0 - t$). Extensive technical data available on request. |
| Material | Spring steel |
| Outer diameter | 46.5 |
| Surface treatment | Phosphated |
| Thickness | 0.60 mm |
| Info | Warning: electroplating of these products may cause hydrogen embrittlement. |

Standards

Technical Specification

| | |
|----------------------|------|
| D _i (H12) | 30.5 |
| F | 153 |
| l ₀ | 1.4 |

Technical Drawing

t

0.6

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS

