



Adjusting ring with set screws DIN 705 A Free-cutting steel Zinc plated with DIN 553 12

Article number	37816.120.001
Brand	-
UBB	500649364824
UNSPSC	31161807
EAN	8717077267510
PKG. of 10	Full Box Only

Technical Parameters

Diameter	12 mm
Material	Free-cutting steel
Surface treatment	Zinc plated

Info

Adjusting rings with $d_2 \leq M10$ are equipped with slotted screws to ISO 7434 (DIN 553), for $d_2 > M10$ these are hex socket set screws to ISO 4027 (DIN 914). Adjusting rings with $d_1 \leq 70$ are provided with one set screw, rings with larger diameter are provided with two set screws. with DIN 553

Standards

DIN	705-A
-----	-------

Technical Specification

b (js14)	12
d1	12
d2 (h13)	22
d3	6
D (mm)	12

Technical Drawing

