



## Parallel pin (dowel pin) with internal thread, hardened, ground DIN 7979 D Steel 60±2HRC Plain 5X12MM

|                |               |
|----------------|---------------|
| Article number | 39090.050.012 |
| Brand          | -             |
| UBB            | 950359916372  |
| UNSPSC         | 31163203      |
| EAN            | 8715492800992 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                    |         |
|--------------------|---------|
| Diameter           | 5 mm    |
| Length             | 12 mm   |
| Material           | Steel   |
| Material technical | 60±2HRC |
| Surface treatment  | Plain   |

Info

The tolerance class of outer diameter d is m6. The nominal length (L tolerance class js15) includes the rounded ends. Shank with slight flat or small groove at the manufacturers discretion.

### Standards

|     |          |
|-----|----------|
| NF  | ≈E27-475 |
| ISO | ≈8735-A  |
| NEN | ≈2464    |
| DIN | 7979-D   |

### Technical Specification

|        |     |
|--------|-----|
| c1 ≈   | 0.5 |
| c2 ≈   | 1.7 |
| d1     | 3   |
| D (mm) | 5   |
| L (mm) | 12  |
| L1     | 12  |
| r ≈    | 5   |

### Technical Drawing



