



Parallel pin (dowel pin) with internal thread, hardened, ground DIN 7979 D Steel 60±2HRC Plain 5X14MM

Article number	39090.050.014
Brand	-
UBB	500645330811
UNSPSC	31163203
EAN	8717077080089
PKG. of 100	Full Box Only

Technical Parameters

Diameter	5 mm
Length	14 mm
Material	Steel
Material technical	60±2HRC
Surface treatment	Plain

Info The tolerance class of outer diameter d is m6. The nominal length (L tolerance class js15) includes the rounded ends. Shank with slight flat or small groove at the manufacturers discretion.

Standards

DIN	7979-D
ISO	≈8735-A
NF	≈E27-475
NEN	≈2464

Technical Specification

c1 ≈	0.5
c2 ≈	1.7
d1	3
D (mm)	5
L (mm)	14
L1	14
r ≈	5

Technical Drawing



