



Split pin (cotter pin) DIN 94
Steel Zinc plated 16X200MM

Article number	39350.160.200
Brand	-
UBB	500644961236
UNSPSC	31163204
EAN	8717077036222
PKG. of 25	Full Box Only

Technical Parameters

Diameter	16 mm
Length	200 mm
Material	Steel
Surface treatment	Zinc plated

Standards

ISO	1234
NF	E25-774
NEN	182
DIN	94

Info	The shape of the split pin ends are at the manufacturer's discretion.For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506.The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters.The tolerance class of the nominal length (L) is js17.
------	--

Technical Specification

a (max.)	6.3
----------	-----

Technical Drawing

b ≈	32
c (max.)	30.8
c (min.)	27
d (min.)	15.1
D (mm)	16
L (mm)	200
d (max.)	15.4

