



Round head rivet DIN 660/124 Steel C4C/C10C Plain 8X10MM

Article number	39400.080.010
Brand	-
UBB	950368004566
UNSPSC	31162201
EAN	8715492821614
PKG. of 250	Full Box Only

Technical Parameters

Diameter	8 mm
Length	10 mm
Head shape	Round head
Material	Steel
Material technical	C4C/C10C
Surface treatment	Plain

Standards

DIN	660/124
ISO	1051
BS	4620

Technical Specification

d1	8
d2	14
d3 (min.)	7.76
D (mm)	8
e (max.)	4
k (js14)	4.8
L (mm)	10

Technical Drawing

