



DIN 661/302 Steel C4C/C10C Plain 4X50MM

Article number	39410.040.050
Brand	-
UBB	500645359877
UNSPSC	31162201
EAN	8717077083073
PKG. of 250	Full Box Only

Technical Parameters

Diameter	4 mm
Length	50 mm
Head shape	Countersunk head
Material	Steel
Material technical	C4C/C10C
Surface treatment	Plain

Standards

DIN	661/302
ISO	1051
BS	4620

Technical Specification

d1	4
d2	7
d3 (min.)	3.87
D (mm)	4
e (max.)	2
k ≈	2
L (mm)	50

Technical Drawing

